

Drive Unit Nomenclature



Mounting for Upright	Shaft Arrangement	High Speed Shaft	Slow Speed Shaft	Option	Nominal Ratio
(Blank)		M <p>Right Angle Shaft</p> <p>Parallel Shaft</p>	(Blank) <p>Solid Shaft</p> <p>Hollow Shaft (Shrink Disk Type)</p>	(Blank) <p>Without Option</p>	Right Angle Shaft
					6.3 56 7.1 63 8 71 9 80 10 90 11.2 100 12.5 112 14 125 16 140 18 160 20 180 22.4 200 25 224 28 250 31.5 280 35.5 315 40 355 45 400 50 450
W Wall Mount (Upright Mounting)		Y <p>Flange for Motor (Right Angle Shaft)</p>	<p>Hollow Shaft (Key Type)</p>	B <p>With Backstop</p>	Parallel Shaft
		J <p>Motor Adapter (Parallel Shaft)</p>			6.3 56 7.1 63 8 71 9 80 10 90 11.2 100 12.5 112 14 125 16 140 18 160 20 180 22.4 200 25 224 28 250 31.5 280 35.5 315 40 355 45 400 50 450 50 450

Drive Unit Selection

Drive Unit
 Selection Tables
 Dimension Tables

